


Our recommendations for printing

Printer settings

For printing your personalized label please click on the button „Print“ in your Adobe® Acrobat® Reader. The printer settings are getting opened.



Please check if all settings are marked as shown above. The “Page Scaling” should be “None” and the “Auto-Rotate and Center”-Option should be checked (see red box above). Then press on „OK“ and your printer will start printing.

Printing and Application Tips

To get the best results please read carefully our advices:

1. You can use a much more stronger paper than normal. Take e.g. a grammage of 135 gr./m². With that you will achieve a better result and the label will be much more stable.
2. Instead of using regular paper in A4, you can use smaller papers like A5/A6. With that you can save unmeant cuttings.
3. Please change your printer settings before printing to color mode to get a premium result.
4. Protect your personalized label with our new transparent covers for SYSTEMER T-LOC. The protective covers can be purchased at your local Festool dealer, order number: 497855
5. Save your personalized label to your local hard drive for a later re-usage.

